





Conductive Anti-Fatigue Mat No. AF-45

EDP No. 621489

e-saving type now available!




Alleviate fatigue caused by standing for a long time





Good for space-saving type of cell production table



Applications

Cell production table; Standing assembly work; Conveyor line with multiple workers, and so on.

RoHS

STAT:CLE series

Conductive Anti-Fatigue Mat No. AF-45 New



This conductive mat can be used on the ESD preventive floor.



EPA Working Mat **Conductive Rubber Mat**

Controlling electro conductivity between 10^6 and 10^7 Ω without influence from the working environment. Ideal for workbenches requiring static electricity measures.



LG-100 EDP No. 621464 SG-100 EDP No. 621461

- ▶ Uniform and stable conductive performance
- ▶ Matte surface finish, reducing reflections for less eye-fatigue
- Heat resistant to dropping solder

Applications	Conductivity	Material	Directi	ve
Designed for use with work benche		NBR+SBF	EPA R	oHS
STRUCTURE Surface layer (static electricity-diffusing rubber)				
COMMON SP	ECIFICATIONS	Backing (conductive)	rubber)	
Model No.	LG-100	SG-10	00	
Color	Light green		Green	
Size	W1.0m×L10m×t2.0m	m W1.0	m×L10m×t2.0mm	
Conductivity	10 ⁶ ≦R≦10 ⁷ Ω	10 ⁶ ≦	R≦10 ⁷ Ω	
Weight	35kg/roll	35kg/	roll	

Surface Resistance Checker

Easy checking of surface resistance on floor or mat

- SRC-01
- ▶ All items necessary for 4 types of measurement in one package

NBR+SBR

- Can also measure temperature and humidity (the values are for reference)
- Applied voltage selector switch enables to measure either the range of $1.0x10^3 \sim 10^5 \Omega$ or of $1.0x10^6 \sim 10^{12} \Omega$.

124.3	
190 54.7	

EDP No. 621604

ACCESORIES
Probe (outer diameter: about Φ66 mm, about 2.3 kg): 2
Curled cord for a body earth (banana plugs at both ends): 1
Curled cord for measurement for the point-to-point resistance and resistance to ground (banana plug/mono plug): 2
Crocodile clip: 1, Large crocodile clip: 1
Stainless plate (230 mm x 142 mm): 1
Stainless plate: 1
Carrying case: 1
9V battery (006P type: manganese dry battery): 1 %The accompanying battery is a sample. It may have run down soon after purchase. Thank you for getting a new battery by yourself.
Manuals

Measurement	Measurement	Measurement	Measurement	Directive
	Resistance between a ground and a points on a surface	Surface resistivity	Volume resistance	C € RoHS

SPECIFICATIONS

Material

OI LOII IOATION	•
Conformity standards	IEC61340-4-1, JIS-C2170
Measurement range	$10^{3}\sim 10^{12}\Omega(\Omega/\text{sq.})$
Applied voltage	10V (R<1.0×106 Ω or $\Omega/sq.)$, 100V (R≥1.0×106 Ω or $\Omega/sq.)$
Display	Triple-digit LCD (\square e \square) ex.: 3.14 e10 \rightarrow 3.14×10 ¹⁰
Power source	9V battery × 1 (Type: 006P, recommended alkaline battery)
L×W×D	190(L)× 101.5 (W) × 54.7 (H) [mm]
Weight	Body: around 340g (including a battery), gross weight: around 6.2kg (including the carrying case)
Operating temperature and humidity	0°C~37°C, 10%~90%RH
Material	Body case: ABS resin

NBB+SBB



For safety purposes, read the instruction manual carefully before using the unit. Do not use this product in an explosion-proof area. A high voltage is applied on this product. Make sure that water, oil, solvents, etc., do not come in contact. Avoid dew condensation as it can result in electric shock or product damage. Keep away metal objects such as tools or needles, or body parts such as fingers, hands or face from the needle electrode because a high voltage is applied on the needle electrode.

17-25, Fukae-kita 2-chome, higashinari-ku, Osaka 537-0001 JAPAN Tel: +81(0)6 6976 7778 Fax: +81(0)6 6972 9441

VESSEL EUROPE

6, avenue du 1er Mai, ZAE Les Glaises, 91120 Palaiseau FRANCE Tel: +33(0)1 69 19 17 42 Fax: +33(0)1 69 19 42 20

E-mail: export@vessel.co.jp URL: http://www.vessel.co.jp/english/

●For improvements, the product specifications, size, price and other information

	may be subject to change without phot hotic
Distributed by	
	Printed in Japan